

# **Super-Luminescent Light Emitting Diode (SLD)**

**TO CAN Packaged Devices** 



#### **Features**

- High power and broad band
- Low coherence length
- Uncooled & Cooled TO package
- Monitor PD is an option

# **Applications**


- Medical diagnostic systems
- Optical Fiber sensor systems
- Illumination

# **IPSDT0804 SLD TO CAN Specifications (Tcase=25°C)**


Parameter	Min.	Тур.	Max.	Unit	Test Condition
Central Wavelength	820	830	850	nm	
3 dB Bandwidth	30	32	-	nm	
Output Power	40	45	-	mW	Flat Window Output
Operating Current	-	250	400	mA	
Forward Voltage	-	-	-	V	
Spectral Ripple	-	0.1	0.5	dB	
Beam Spread Angle:	-	-	-		
- Parallel	-	10	25	degree	
- Vertical	-	38	45	degree	


Detailed Information about operation/storage temperature available upon request: Contact <a href="mailto:sales@inphenix.com">sales@inphenix.com</a> for more details





Pin#	Connection
1	SLD Anode
2	SLD Cathode, PD
	Cathode and Case
3	PD Anode






 $\phi$ 9 mm TO-CAN (TO5/TO9/TO39)


All information contained herein is believed to be accurate and is subject to change without notification. No responsibility is assumed. Please contact InPhenix for more information. InPhenix and the InPhenix logo are trademarks of InPhenix Inc. All rights are reserved.





Pin#	Connection
1	PD Anode
2	SLD Cathode, PD Cathode and Case
3	SLD Anode
4	

Pigtail Information				
Connector	TBD			
Fiber	SMF			
Fiber Length	0.5 m			



 $\phi$ 5.6 mm Pigtailed Coaxial Device (TO56 Header)



#### **Part Numbering System**

IPSDTXXXX	lacksquare	
Model- IPSDT0701: 750nm SLD TO CAN		
IPSDT080X: 820nm SLD TO CAN IPSDT090X: 900nm SLD TO CAN		
IPSDT13XX: 1310nm SLD TO CAN IPSDT150X: 1550nm SLD TO CAN		
Package- 7: TO 56 8: TO 8 9: TO 9 Fiber Type: 0: No Cap 1: Single Mode 5: Ball Lens 6: Flat Glass 7: Aspheric Lens		
Jacket Type: 0: No Jacket 1: 900 µm 2: 250 µm tight buffer Connector Type:		
0: No Connectors		

- 3: FC/APC
- 4: FC/UPC
- 7: SC/APC
- 8: SC/UPC

## **Back Facet Monitor:**

Available upon request

Example: IPSDT0801-9700: 820nm SLD, TO9 package with Aspheric lens.

## **Corporate Office**

250 North Mines Rd Livermore, CA 94551 Tel: 925.606.8809 Fax: 925.606.8810 www.inphenix.com sales@inphenix.com